



Cordless Worklight ML011G / DML817 / ML107



40V^{Li-ion}_{max}

18V^{Li-ion}_{LITHIUM-ION}

12V^{max}_{LITHIUM-ION}

Max luminous flux	
ML011G / DML817	ML107
300 lm	200 lm



photo: ML011G



photo: DML817



photo: ML011G



photo: DML817



photo: ML107

ML011G



USB



DML817



USB



ML107



USB



LED light

Daylight white LED
(with color temperature
of 5,000K)



Three lighting modes

Equipped with 2 LEDs, one for sidelighting and the other for uplighting, for wide-angle illumination.



Mode memory function:
The appliance saves the
lighting mode at the time
when turned off by press
and holding the light switch
button.
(This mode is remembered
even if the battery is
removed after that.)


Supplied with Warm white lamp shade

Allowing for changing to warm white tone
lighting (with color temperature of 2,500K),
which has a high relaxing effect



Compact design

Minimal size of the appliance
has been achieved for space
saving use and storage by
designing it on the basis of the
size of compatible battery.



USB output port

ML011G/DML817:
1 port (Type A for DC5V/2.4A)
ML107:
1 port (Type A for DC5V/2.1A)
• With Auto-off function(after
30 minutes of no operation)
• With Output indication lamp



Also can be used for downlighting

With optional "Strap with hook"
fastened to the two Strap holes
on the appliance, the light can
be used for downlighting by
hanging it upside down.



Charging Time

40V ^{Li-ion} max	Fast Charging		18V LITHIUM-ION	Fast Charging		12V ^{max} LITHIUM-ION	Fast Charging	
	DC40RA	DC40RC		DC18RC	DC18SD		DC10SB	DC10WD
*1 BL4020 2.0Ah	22 min	30 min	BL1815N 1.5Ah	15 min	30 min	BL1016 1.5Ah	22 min	50 min
*1 BL4025 2.5Ah	28 min	38 min	BL1820B 2.0Ah	24 min	45 min			
*1 BL4040 4.0Ah	45 min	67 min	BL1830B 3.0Ah	22 min	60 min	BL1021B 2.0Ah	30 min	70 min
*1 BL4050F 5.0Ah	50 min	85 min	BL1840B 4.0Ah	36 min	90 min			
*1 BL4080F 8.0Ah	76 min	170 min	BL1850B 5.0Ah	45 min	110 min	BL1041B 4.0Ah	60 min	130 min
			BL1860B 6.0Ah	55 min	130 min			

*1 Recommended battery

Accessories

Strap with hook

Part No. SE00001178

Strap with hook is fastened to
the two Strap holes on the
appliance, the light can be used
for downlighting by hanging it
upside down.



Cordless Worklight

ML011G / DML817 / ML107

	ML011G	DML817	ML107
Illuminance (at 0.5 m from the light source)	Sidelighting + Uplighting / Sidelighting only / Uplighting only: 240 / 190 / 190 lx	Sidelighting + Uplighting / Sidelighting only / Uplighting only: 240 / 190 / 190 lx	Sidelighting + Uplighting / Sidelighting only / Uplighting only: 175 / 130 / 130 lx
Luminous flux	Sidelighting + Uplighting / Sidelighting only / Uplighting only: 300 / 150 / 150 lm w/ BL4040, at 300 lm: 37 w/ BL4040, at 150 lm: 64 w/o Battery: 107 x 77 x 50 mm (4-1/4 x 3 x 2")	Sidelighting + Uplighting / Sidelighting only / Uplighting only: 300 / 150 / 150 lm w/ BL1860B, at 300 lm: 28 w/ BL1860B, at 150 lm: 49 w/o Battery: 107 x 77 x 50 mm (4-1/4 x 3 x 2")	Sidelighting + Uplighting / Sidelighting only / Uplighting only: 200 / 100 / 100 lm w/ BL1041B, at 300 lm: 17 w/ BL1041B, at 150 lm: 29 w/o Battery: 92 x 54 x 47 mm (3-5/8 x 2-1/8 x 1-7/8")
Run time (hrs)			
Dimensions (L x W x H)			
Net weight	0.19 kg (0.42 lbs.)	0.21 kg (0.46 lbs.)	0.29 kg (0.13 lbs.)

Standard Equipment : Warm color cover

not covered by EPTA-Procedure

Items of standard equipment and specifications may vary by country or area.

Makita Corporation

3-11-8 Sumiyoshi-cho, Anjo, Aichi, 446-8502 Japan

PRINTED IN JAPAN 202305